



VISHAY INTERTECHNOLOGY, INC.



THE FARNELL
SUPER 12

FEATURED PRODUCTS



2017



element14

www.vishay.com/ref/2017s12



Table of Contents



SQJQ480E

TrenchFET® Gen IV MOSFET


01



T59 Series

vPolyTan™ Polymer Capacitors

02



VCNL4035X01

Optical Sensor

03



WSLF2512

6 W Power Metal Strip® Resistor

04



VTVS5V0ASM to VTVS63GSMF

400 W Transient Voltage Suppressor Diodes

05



IHLE-5A Series

High Current Inductors with E-Field Shield

06





SiC462

Synchronous microBUCK® Regulator

07



MKP1847H

AC Filtering Film Capacitor

08



10 A to 30 A FRED Pt®

Ultrafast Rectifiers in SMPD Package

09



299 PHL-4TSI

Aluminum Electrolytic Capacitors

10



SiRA20DP

TrenchFET® Gen IV MOSFET

11




SMM0204

Thin Film MELF Resistor

12





SQJQ480E

TrenchFET® Gen IV MOSFET

80 V, 3 m Ω N-Channel MOSFET in
PowerPAK® 8x8L Package

01



FEATURES

- TrenchFET® power MOSFET
- AEC-Q101 qualified
- 100 % R_g and UIS tested
- Fully lead (Pb)-free device
- Low profile height: 1.9 mm
- PowerPAK® SO-8 and PowerPAK® 8x8L packages achieve the best R_{DS}, Q_g, and Q_{OSS} by minimizing the package resistance and parasitic resistance

APPLICATIONS / MARKET SEGMENTS

- Automotive
- Transportation / intralogistics



T59 Series

vPolyTan™ Polymer Capacitors

Low ESR, High Energy Polymer
Capacitors in MAP Package

02




FEATURES

- Wide capacitance range: 15 μF to 470 μF
- Voltage ratings up to 75 V
- Ultra low ESR down to 25 m Ω
- Patented MAP packaging offers 25 % improvement in volumetric efficiency to yield the industry's highest capacitance density
- Low ESR: multi-anode construction reduces ESR by 50 %
- L-terminations reduce equivalent series inductance (ESL) by 33 % while improving the electrical and mechanical connection to the PCB

APPLICATIONS / MARKET SEGMENTS

- Bulk energy storage in solid-state drives
- Filtering and voltage holdup in power conversion applications



VCNL4035X01

Optical Sensor

Integrated Proximity and Ambient Light
Sensor for Gesture Applications

03




FEATURES

- AEC-Q101 qualified
- 16-bit resolution for ambient light and proximity sensors
- Integrated current driver with internal logic to drive up to three IREDS for gesture recognition
- Excellent background light cancellation
- Outstanding sensitivity allowing high object detection distance
- Low profile package: 0.75 mm

APPLICATIONS / MARKET SEGMENTS

- Displays
 - Wake-up and touch screen locking
 - Backlight and contrast control
- Gesture recognition with two or three external emitters to detect swipe gestures



WSLF2512

6 W Power Metal Strip® Resistor with
Low Resistance and Low TCR

04




FEATURES

- High power rating up to 6 W
- Low resistance values down to 0.0003 Ω
- TCR down to 70 ppm/°C
- Small case for power rating: 2512

APPLICATIONS / MARKET SEGMENTS

- Current sensing, voltage division, and pulse applications in power management for:
 - Automotive electronic controls (engine, transmission, anti-lock brakes, audio, and climate controls)
 - Inverter controls for down-hole test and measurement equipment
 - Inverter controls for HVAC systems
 - VRMs for servers
 - Current sensing in power semiconductor modules



VTVS5V0ASMF to VTVS63GSMF

400 W Transient Voltage Suppressor
(TVS) Diodes in SMF Package

05




FEATURES

- 400 W peak pulse power capability with 10/1000 μ s waveform
- 2 % tolerance of avalanche breakdown voltage
- Low profile SMF package (1 mm height)
- Low clamping ratio
- High surge current
- Wave and reflow solderable
- Operating temperature: -55 °C to +175 °C

APPLICATIONS / MARKET SEGMENTS

- Line transient voltage protection in space-constrained electronics such as laptops, notebooks, tablets, external hard drives, and more



IHLE-5A Series High Current Inductors with E-Field Shield

Provide 20 dB Electric Field Reduction
at 1 cm for Automotive Applications

06




FEATURES

- Integrates e-field shield into an IHLP® inductor package
- Reduces e-field up to 20 dB at 1 cm
- High efficiency with typical DCR from 1.55 mΩ to 167 mΩ
- Wide range of inductance values from 0.22 μH to 47 μH
- Available in three case sizes: 2525, 3232, and 4040
- Rated currents to 36 A and handle high transient current spikes without saturation
- Available in any standard IHLP inductance value
- Automotive Grade and AEC-Q200 qualified

APPLICATIONS / MARKET SEGMENTS

- DC/DC converter circuits near noise-sensitive components
- Automotive control circuitry
- Computer and other high current, noisy power supplies



SiC462

Synchronous microBUCK[®] Regulator

4.5 V to 60 V Buck Regulator Capable of Delivering Up to 75 W Output Power

07



FEATURES

- Scalable solution for 3 A, 6 A, and 10 A
- Stable with any output capacitor
- 100 kHz to 1.5 MHz operating frequency
- Low quiescent current – 250 μ A, low shutdown current
- Single supply operation down to 5 V with internal linear regulator
- Protection and monitoring: OVP, OCP, UVP, OTP, UVLO, power good
- Operating ambient temperature: -40 °C to 105 °C

APPLICATIONS / MARKET SEGMENTS

- Industrial and automation
- Industrial computing
- Base station power supplies
- Wall transformer regulation
- Robotics
- Drones
- Battery management systems
- Power tools
- Vending, ATM, and slot machines



MKP1847H

AC Filtering Film Capacitor

Robust Design for High Humidity
Environments

08




FEATURES

- 85 °C, 85 % relative humidity, 1000 h at rated UNAC
- Rated voltages: 250 VAC, 310 VAC, 350 VAC, and 480 VAC
- Rated capacitance range: 1 µF to 35 µF
- Segmented film
- UL 810 (electrical pending)

APPLICATIONS / MARKET SEGMENTS

- Outdoor applications
 - Inverters and converters
- High power supplies and large drives
- UPS
- Renewable energy
- Welding equipment
- AC harmonic filters



10 A to 30 A FRED Pt[®]

Ultrafast Rectifiers in SMPD Package

Offer Higher Power Density

09



FEATURES

- High operating temperature up to 175 °C
- Low forward voltage drop down to 0.75 V typical with fast recovery time down to 25 ns
- Soft recovery behavior over a temperature range of -40 °C up to 175 °C
- Low profile (< 1.7 mm height) SMPD (TO-263AC) package is footprint-compatible to TO-263 (D2PAK) package
- Available in AEC-Q101 qualified and standard versions

APPLICATIONS / MARKET SEGMENTS

- Automotive
 - EV / HEV battery charging systems
 - Power supply PFC
- Industrial
 - APD in inverters for motor drives, UPS, and LED and HID lighting systems



299 PHL-4TSI

Aluminum Electrolytic Capacitors

Power High Ripple Current Long Life
4-Terminal Snap-In

10




FEATURES

- Large types, minimized dimensions, cylindrical aluminum case, insulated with a blue sleeve
- Pressure relief on the side of the aluminum case
- Very long useful life: 5000 h at 105 °C
- Temperature range up to 105 °C
- Four terminals for stable mounting and keyed polarity
- Allows replacement of bus bars and screw terminals by lower cost PC board and solder process
- High ripple current capability

APPLICATIONS / MARKET SEGMENTS

- Switched mode power supplies
- Renewable energy power converters
- Energy storage in pulse systems



SiRA20DP

TrenchFET® Gen IV MOSFET

25 V, 0.58 mΩ N-Channel MOSFET

Provides Lowest Maximum $R_{DS(on)}$

11



FEATURES

- Provides the lowest maximum $R_{DS(on)}$ rating at $V_{GS} = 10\text{ V}$
- Increases power density as the $R_{DS(on)}$ cuts conduction power loss
- Provides the lowest Q_g for devices with maximum $R_{DS(on)} < 0.6\text{ m}\Omega$
- Low Q_g enables high efficiency for DC/DC conversion
- Available in the PowerPAK® SO-8 package

APPLICATIONS / MARKET SEGMENTS

- OR-ing
- Battery management and load switching
- Synchronous rectification
- Synchronous buck



SMM0204

Thin Film MELF Resistor

Perfect choice for most fields of modern electronics where reliability and stability are of major concern

12



FEATURES


- Advanced metal film technology
- AEC-Q200 qualified
- Approval acc. EN 140401-803 available on request
- Excellent stability in different environmental conditions
- Best in class pulse load capability
- Intrinsic sulfur resistance

APPLICATIONS / MARKET SEGMENTS

- Automotive
- Telecommunication
- Industrial
- Medical equipment



VISHAY INTERTECHNOLOGY, INC.



element14

This document is subject to change without notice. The products described herein and this document are subject to specific disclaimers, set forth at www.vishay.com/doc?91000

