

**Data connections for the factory of the future**  
**Single Pair Ethernet Solutions**  
Industrial Internet of Things



**Weidmüller** 

## Single Pair Ethernet

### The network infrastructure for Industrial IIoT

In the factory of the future, machines and systems will be connected to each other consistently via a data infrastructure. These cyber-physical systems can act independently in the Industrial Internet of Things (IIoT), communicate in real time, and control production processes. In order to enable this, a continuous network with high-performance data connections from the sensor to the cloud is required. This pushes conventional Ethernet systems to their limits.

Single Pair Ethernet (SPE) facilitates the extension of the Ethernet to the sensor. It is compact, flexible, and enables high ranges. This means that data connections are achievable in situations where conventional Ethernet systems have reached their limits. SPE provides for the extension of existing installations and supports consistent communication based on the Ethernet protocol. Indeed, SPE is considered by Weidmüller as the missing component needed to close the current gap in the supply of standard Ethernet at field level.

SPE runs at the same transmission speeds as conventional Ethernet but with simplified 2-wire cabling technology and data lines up to 1,000 m in length. Together with other new technologies such as TSN, OPC-UA, or 5G, SPE enables both continuous IP communication between the server and the cloud, as well as supplying up to 60 Watts of power in complex IIoT solutions through PoDL (Power over Data Line).



## Versatile use in different applications

### SPE applications in practice

SPE solutions are particularly suitable for infrastructures in mechanical and plant engineering, process technology, and building infrastructure – in other words, wherever data must be transmitted continuously and over long distances. With SPE, field devices, sensors and actuators can be integrated directly into an existing Ethernet environment without additional gateways and interfaces.



Factory Automation

#### Examples of the use of SPE in buildings:

Building automation systems, lighting systems, control systems for lifts and escalators, surveillance systems, access control systems, security and fire alarm systems

#### Examples for industrial applications:

Industrial automation, process automation, robotics, mechanical engineering, conveyor technology, quality control, agricultural machinery



Building Infrastructure



Process Automation



Intrinsically safe process industry with Ethernet-APL



## The new standard for high demands

### Continuous communication from the sensor to the cloud

Single Pair Ethernet can transfer data and power using only one twin wire. This enables both end-to-end IP communication between server and cloud, as well as power supply in complex IIoT solutions. SPE connectors and devices therefore are particularly efficient and future-oriented and at the same time extremely compact.

**In addition to the existing connectors, switches are also available on request:**

#### Unmanaged Switches 10Base-T1L (and 100Base-T1)

The unmanaged switch offers the solution for reliable and efficient networking. It enables the bridging of large distances of up to 1,000 m through the SPE standard 10Base-T1L (10 MBit/s). Using this switch eliminates the need for subsystems or gateways, simplifying the network infrastructure and reducing complexity.

- Simple and space-saving installation, as both data transmission and power supply are provided via only one pair of wires (PoDL classes 10 - 14, up to 30 W, SCCP support).
- Weidmüller's unmanaged switch is compatible with all Ethernet and IP-based protocols and can be used universally.
- Provides a reliable and efficient way to optimise network connectivity and increase system efficiency.



## SPE connectors for the industry

### Advantages of SPE connectors at a glance

**The market requirements for data connectors in the field level are:**

- Smallest, most compact design
- Easy to connect / safe, fast installation
- High robustness for use in industrial environments
- Future-proof through international standards

#### Miniaturisation

#### Industrial suitability



Simplicity

Future-proof



## Miniaturisation

### Particularly compact

#### Miniaturisation of SPE connectors according to IEC 63171-2

Weidmüller has been developing user-friendly connectors for industrial use, according to IEC63171-2. With a pitch of 7.62mm the compact connector system saves up to 50% space in comparison to RJ45 interfaces. The vertical arrangement of the two contacts allows a very high packing density. This enables device manufacturers to save valuable space on the PCB and to build smaller devices. This reduces port costs in device construction and effectively saves space in the control cabinet.

#### Small mating face


- Currently the smallest mating face according to IEC 63171 on the market

#### High packing density

- Double the packing density compared to RJ45 connectors
- Doubling of the interfaces with the same housing contour
- Only 20% of the volume of an RJ45 jack
- Minimum space requirement in the device

#### Easy IP67-integration

- Can be integrated into standard M8 housings and connectors as with I/O-Link or PROFINET
- M8 connectors with male and female contacts available
- Front and rear panel mounting with male and female contacts supported
- Simple integration in M8 sensors
- Inverse M8 system possible



## Industrial suitability

### Made for highest demands

#### The industrial suitability of SPE connectors

Originally developed for automotive applications, the aim of single pair ethernet technology was to realise the most efficient infrastructure capable of delivering high performance with as little cabling as possible. There are similar expectations within industry applications and building automation where the number of intelligent end devices in the plant is increasing but the amount of available space is not. Weidmüller SPE connector solutions deliver long cable lengths, a compact design that is simple, robust and vibration-proof, as well as being insensitive to electromagnetic influences.

#### Mechanical robustness

- Robust metal housing with metal snap-in hooks
- Safe industrial double contacting compared to single-sided contacting RJ45
- Shock resistant and vibration resistant according to IEC 60068
- Stable latching with lateral forces

#### EMC Compatibility

- Coupling attenuation at 600 MHz according to IEEE 802.3
- Additional burst test according to IEC 61000-6-2
- Optimum shield connection on the PCB due to four symmetrical legs

#### Industrial suitability

- PCB connectors for environments up to pollution degree 2
- Impulse voltage strength of 2.25 kV according to IEEE 802.3
- Optimum contact distance for 100 Ohm systems







# Single Pair Ethernet System Alliance

## On the path to a uniform market standard The SPE System Alliance and its objectives

The Single Pair Ethernet System Alliance is an open consortium of leading technology companies and scientific organisations from various industries and fields of application. Manufacturers of sensors, cables, connectors, measuring devices, semiconductors, switches and end devices work together to establish SPE solutions for a wide range of applications.

### The mission:

- Promoting exchange between experts from a wide range of technology areas.
- Building up know-how for fast and reliable technology implementation.
- Demonstrating the holistic benefits of the Ethernet-only approach.
- Developing a proof of concept for SPE interoperability.
- Raising public awareness of SPE by increasing marketing efforts, growing membership, collaborating with other SPE organisations and facilitating access to SPE products.

### The goal:

Achieving technical maturity and a broad market acceptance, providing users with the highest level of future security.

Further information about the SPE System Alliance can be found at [www.singlepairethernet.com](http://www.singlepairethernet.com)



### Members

Stand: March 2024



... and more.

# Single Pair Ethernet Solutions

## Ordering data

### IP20 SPE cabling

Type	Versions	Qty.	Order No.
	IE-S1DS2VE0010T01T01-E Patch cable overmoulded, IP 20, Female-Female, 1m	1	2725850010
	IE-S1DS2VE0020T01T01-E Patch cable overmoulded, IP 20, Female-Female, 2m	1	2725850020
	IE-S1DS2VE0030T01T01-E Patch cable overmoulded, IP 20, Female-Female, 3m	1	2725850030
	IE-S1DS2VE0050T01T01-E Patch cable overmoulded, IP 20, Female-Female, 5m	1	2725850050
	IE-S1DS2VE0100T01T01-E Patch cable overmoulded, IP 20, Female-Female, 10m	1	2725850100
	IE-S1DS2VE0150T01T01-E Patch cable overmoulded, IP 20, Female-Female, 15m	1	2725850150
	IE-S1DS2VE0400T01T01-E Patch cable overmoulded, IP 20, Female-Female, 40m	1	2725850400

Other lengths on request

### IP67 SPE cabling

Type	Versions	Qty.	Order No.
	IE-S1DS2VE0020TM1TM1-E Patch cable overmoulded, M8 IP 67, Female-Female, 2m	1	2726050020
	IE-S1DS2VE0050TM1TM1-E Patch cable overmoulded, M8 IP 67, Female-Female, 5m	1	2726050050
	IE-S1DS2VE0100TM1TM1-E Patch cable overmoulded, M8 IP 67, Female-Female, 10m	1	2726050100
	IE-S1DS2VE0150TM1TM1-E Patch cable overmoulded, M8 IP 67, Female-Female, 15m	1	2726050150
	IE-S1DS2VE0200TM1TM1-E Patch cable overmoulded, M8 IP 67, Female-Female, 20m	1	2726050200
	IE-S1DS2VE0400TM1TM1-E Patch cable overmoulded, M8 IP 67, Female-Female, 40m	1	2726050400

	IE-S1DS2VE0020TM1TM2-E Patch cable overmoulded, M8 IP67, Female-Male, 2m	1	2726060020
--	--	---	------------

	IE-S1DS2VE0020TM2TM2-E Patch cable overmoulded, M8 IP67, Male-Male, 2m	1	2726070020
---	--	---	------------

Other lengths on request

### Connecting components

Type	Versions	Qty.	Order No.
	IE-PS-SP0-S-FH-180 Field attachable plug IP20, Female	1	2726040000
	IE-AD-SP0-P-SPM-P-90 SPE IP20 to SPE M8 adapter, Male	1	2814400000
	IE-BI-SP0-C SPE IP20 coupling, Male, for installation in service interface FrontCom® Vario	10	2861260000
	IE-FCM-SP0-C FrontCom® Micro Service interface IP65 with SPE coupling, Male	1	2870820000
	IE-TO-SP0-C-LP DIN rail outlets IP20 with SPE coupling, Male	1	2870790000

### PCB components

Type	Versions	Qty.	Order No.
	IE-PCB-SP0-P-90V-THR PCB connector, IP20, 90°, THR Male	100	2726010000
	IE-PCB-SP0-P-90V-THR-YG/YG PCB connector, IP20, 90°, LED, THR, Male	100	2795120000
	IE-PCB-SP0-P-180V-THR PCB connector, IP 20, 180°, THR, Male	100	2795170000
	IE-BHD-SPE-M8-OT-FP M8 Device housing, front panel mounting	10	2726020000
	IE-BHD-SPE-M8-OT-BP M8 Device housing, back panel mounting	20	2726030000
	IE-BHD-SPE-BP-CN-M10X0.75 Locknut for M8 socket housing	10	2739640000
	IE-PCB-SPM-P-180-THR M8 SPE insert, 180°, THR, Male	100	2735920000
	IE-PCB-SPM-P-180-SMD M8 SPE insert, 180°, SMD, Male	100	2795110000
	IE-PCB-SPM-P-90-THR M8 SPE insert, 90°, THR, Male	100	2795100000



## Ethernet-APL

### The two-wire solution for the process industry

Ethernet-compatible interfaces are increasingly needed in the process industry to access data from the field via IIoT. More and timely information is required from sensors and devices, even over long distances. This requires the integration of IIoT devices into the network infrastructure.

Ethernet-APL as an internationally standardised two-wire solution enables direct access right down to the field and device level. This leads to increased system availability and access to production data.

#### Advantages of Ethernet-APL

- High data rates: 10 Mbit/s communication with ranges of up to 1,000 m in accordance with IEEE 802.3cg-2019.
- PoDL (Power over data line): Supports remote power supply in accordance with IEEE 802.3bu.
- Direct connection to field devices: Integration of sensors and actuators.
- Scalability: Ideal for networking small to large industrial systems.
- Increased system availability through information on individual devices.
- No gateway required between field and company IT.



## Ethernet-APL and Single Pair Ethernet in comparison

### What is the difference between APL and SPE?

	IEEE 802.3 cg Standards					
	APL 10BASE-T1L with 2-WISE		SPE 10BASE-T1L with PODL			
	Heavy Process	Light Process	Factory Automation	Logistics / Warehousing	Building Automation	Others
<p><b>While SPE primarily addresses industrial factory automation and building infrastructure, APL is aimed at the process industry with consideration of additional intrinsic safety for use in explosion-protected areas</b></p>	Oil & Gas Chemical Pharma	Water / Waste Water Pharma Food & Beverage	Industrial Automation Robotics, Process Automation	Conveyor Technology, Quality Control	Lighting- Control Systems Monitoring Access Control	
Ethernet in Industry Applications						

	Ethernet-APL	Single Pair Ethernet
<b>Technology</b>	Two-wire technology	Two-wire technology
<b>Ethernet Standards</b>	10BASE-T1L, IEC TS 60079-47 (2-WISE)	10Base-T1S, 10Base-T1L, 100Base-T1, 1000Base-T1
<b>Data transmission</b>	10 Mbit/s	10 Mbit/s up to 10 Gbit/s
<b>Cable / conductor length</b>	Up to 1,000 m	15 to 1,000 m
<b>Main application</b>	Process industry	Factory automation and building infrastructure
<b>Special features</b>	The extension of the 10BASE-T1L standard in accordance with IEEE 802.3cg includes additional safety precautions that are specially tailored to the needs of the process industry in potentially explosive atmospheres.	Miniaturisation, industrial suitability, simplicity, future-proofing
<b>Connection technology</b>	Classic terminal blocks with screw or tension spring connection, like Omnimate® PCB components, built-in and field-attachable connectors (M12).	Connectors with miniaturised mating faces, patch cables, field attachable plugs, M8 adapters as well as IP20 and IP67 sockets in different outlet directions.

# Ethernet-APL Solutions

## Ordering data

### PCB components

	Type	Versions	Qty.	Order No.
	LMF APL 5.00/03/180 3.5SN BX	PCB terminal block, 5.00 mm, number of poles: 3, 180°, PUSH IN	90	2873470000
	LMF APL 5.00/03/90 3.5SN BX	PCB terminal block, 5.00 mm, number of poles: 3, 90°, PUSH IN	90	2873480000
	LM APL 5.08/03/135 3.5SN OR BX	PCB terminal block, 5.08 mm, number of poles: 3, 135°, tension clamp connection	500	2873490000
	LM APL 5.08/03/90 3.5SN OR BX	PCB terminal block, 5.08 mm, number of poles: 3, 90°, tension clamp connection	500	2873500000
	BLZP APL 5.00HC/03/180F SN OR BX	PCB connector, female connector, 5.00 mm, number of poles: 3, 180°, tension clamp connection	72	2872550000
	MPS APL 5/03 S F2 TN B B D D	PCB connector, female connector, 5.00 mm, number of poles 3, 180°, SNAP IN	114	8000094097

### M12 connectors

	Type	Versions	Qty.	Order No.
	SAIBM-4/8S-M12 4P A-ZF	Field attachable plug connector, M12, socket, straight	1	1784740002
	SAISM-4/8S-M12 4P A-ZF	Field attachable connector, M12, male, straight	1	1304280000
	SAIE-M12S-4-0.5U-PG9	Built-in connector, M12, male, straight, mounting thread: PG 9, number of poles: 4, wire/cable length: 0.5 m, front panel mounting	1	1861220000
	SAIE-M12B-4-0.5U-PG9	Built-in plug, M12, female, straight, mounting thread: PG 9, no. of poles: 4, wire/cable length: 0.5 m, front panel mounting	1	1861250000

### Accessories

	Type	Versions	Qty.	Order No.
	SH ETH U	Shielding bracket, accessories, screw flange, galvanised, silver-grey, box	25	2903230000



## Weidmüller – Your partner in Smart Industrial Connectivity

As experienced experts we support our customers and partners around the world with products, solutions and services in the industrial environment of power, signal and data. We are at home in their industries and markets and know the technological challenges of tomorrow. We are therefore continuously developing innovative, sustainable and useful solutions for their individual needs. Together we set standards in Smart Industrial Connectivity.

We cannot guarantee that there are no mistakes in the publications or software provided by us to the customer for the purpose of making orders. We try our best to quickly correct errors in our printed media.

All orders are based on our general terms of delivery, which can be reviewed on the websites of our group companies where you place your order. On demand we can also send the general terms of delivery to you.

Weidmüller Interface GmbH & Co. KG  
Klingenbergstraße 26  
32758 Detmold, Germany  
T +49 5231 14-0  
F +49 5231 14-292083  
[www.weidmueller.com](http://www.weidmueller.com)

Personal support can  
be found on our website:  
[www.weidmueller.com/contact](http://www.weidmueller.com/contact)

Made in Germany

04/2024/TDFP1